



Part number

CAC 06 L



Brief description:

hoods with 2 pegs, size "44.27", without entry, to be pierced, metal version, IP66

Product description		Approvals / Standards	
Version	metal version	Quality mark	 (type:4/4X/12),  , EAC
Series	hoods for single lever	Conformity	CQC, CE
Product type	with 2 pegs	General ordering information	
Variant	without entry, to be pierced	EAN13 code	8015747005647
Family	CLASS enclosures	Tariff number	85369095
Size	size "44.27"	Packaging Information	
Technical data		Packaging length	255,00 mm
Operating temperature range (min, max)	-40°C ... +125°C	Packaging height	150,00 mm
Material	metal	Packaging width	180,00 mm
IP degree of protection	IP66 (and IP69K DIN 40050 - 9)	Packaging weight	3,20 kg
Further technical details		Packaging volume	6,89 dm ³
Weight	160,00 g	Packaging description	Carton box
		Packaging quantity	20 Pcs
		Packaging EAN code	8015747005654
		Sub-packaging weight	0,80 kg
		Sub-packaging description	Plastic packaging
		Sub-packaging quantity	5 Pcs
		Sub-packaging EAN barcode	8015747005661