

Part number

# CAV 16 L221



## Brief description:

hoods with 2 pegs, size "77.27", top entry, Pg21 x 2, metal version, IP66

### Product description

<b>Version</b>	metal version
<b>Series</b>	hoods for single lever
<b>Product type</b>	with 2 pegs
<b>Variant</b>	top entry
<b>Style</b>	high construction
<b>Family</b>	CLASS enclosures
<b>Size</b>	size "77.27"

### Technical data

<b>Operating temperature range (min, max)</b>	-40°C ... +125°C
<b>Material</b>	metal
<b>IP degree of protection</b>	IP66 (and IP69K DIN 40050 - 9)
<b>Cable entry</b>	Pg21 x 2

### Further technical details

<b>Weight</b>	261,00 g
---------------	----------

### Approvals / Standards

<b>Quality mark</b>	 (type:4/4X/12),  , EAC
<b>Conformity</b>	CQC, CE

### General ordering information

<b>EAN13 code</b>	8015747009560
<b>Tariff number</b>	85369095

### Packaging Information

<b>Sub-packaging weight</b>	1,31 kg
<b>Sub-packaging description</b>	Plastic packaging
<b>Sub-packaging quantity</b>	5 Pcs
<b>Sub-packaging EAN barcode</b>	8015747244688