

Part number

CAVR 16.29



Brief description:

hoods for two levers, size "77.27", top entry, Pg29, 180 °C version, IP65

Product description

Version	180 °C version
Series	hoods for two levers
Product type	with 4 pegs
Variant	top entry
Style	high construction
Family	CLASS enclosures
Size	size "77.27" 180°C version

Technical data

Operating temperature range (min, max)	-40°C ... +180°C
Material	metal
IP degree of protection	IP65
Cable entry	Pg29

Further technical details

Weight	195,00 g
--------	----------

Approvals / Standards

Quality mark	 (type:4/4X/12),  , EAC
Conformity	CQC, CE

General ordering information

EAN13 code	8015747010405
Tariff number	85369095

Packaging Information

Sub-packaging weight	0,98 kg
Sub-packaging description	Plastic pakaging
Sub-packaging quantity	5 Pcs
Sub-packaging EAN barcode	8015747010412