

Part number

C DFA 6A



Brief description:

6A contacts for interface silver and gold plated, 6A female contacts for female inserts, with terminal Ø 1 mm

Product description		Approvals / Standards	
Series	6A female contacts for female inserts	Conformity	CQC, CE
Product type	6A contacts for interface silver and gold plated	General ordering information	
Style	6A female contacts for female inserts, with terminal Ø 1 mm	EAN13 code	8015747014786
Family	6A contacts for interface	Tariff number	85369095
Technical data		Packaging Information	
Current	6 A	Packaging length	112,00 mm
Operating temperature range (min, max)	-40°C ... +125°C	Packaging height	95,00 mm
Contact type	silver plated	Packaging width	117,00 mm
Further technical details		Packaging weight	0,72 kg
Weight	0,90 g	Packaging volume	1,24 dm ³
		Packaging description	Carton box
		Packaging quantity	800 Pcs
		Packaging EAN code	8015747225397
		Sub-packaging weight	0,09 kg
		Sub-packaging description	Plastic box
		Sub-packaging quantity	100 Pcs
		Sub-packaging EAN barcode	8015747014793