

Part number

CHOR 06 L16



Brief description:

surface mounting housings with 1 lever, size "104.62", 1" 1/4 NPT, metal version, IP66

Product description

| | |
|--------------|----------------------------|
| Version | 180 °C version |
| Series | hoods for single lever |
| Product type | with 2 pegs |
| Variant | side entry |
| Family | CLASS enclosures |
| Size | size "44.27" 180°C version |

Technical data

| | |
|--|--------------------------------|
| Operating temperature range (min, max) | -40°C ... +180°C |
| Material | metal |
| IP degree of protection | IP66 (and IP69K DIN 40050 - 9) |
| Cable entry | Pg16 |

Approvals / Standards

| | |
|--------------|---|
| Quality mark |  (type:4/4X/12),  , EAC |
| Conformity | CQC, CE |

General ordering information

| | |
|---------------|---------------|
| EAN13 code | 8015747020503 |
| Tariff number | 85369095 |

Packaging Information

| | |
|---------------------------|-------------------|
| Sub-packaging description | Plastic packaging |
| Sub-packaging quantity | 5 Pcs |
| Sub-packaging EAN barcode | 8015747020510 |