

Part number
CKX 03 I



Brief description:

bulkhead mounting housings with single lever, size "21.21", thermoplastic version, IP44, IP66/IP67 degree of protection with CKR 65 kit or CKR 65 D kit.

Product description	
Version	thermoplastic version
Series	Bulkhead mounting housings with 1 lever
Product type	with stainless steel lever
Style	white colour, RAL 7035
Family	CK thermoplastic enclosures
Size	size "21.21"
Technical data	
Material	thermoplastic
IP degree of protection	IP44 (IP66/IP67 with CKR 65/CKR 65 D kits)
Further technical details	
Weight	20,00 g

Approvals / Standards	
Quality mark	CE type: 12, (type 4/4X only with kit CKR 65 or CKR 65 D),  , EAC
Conformity	CQC, CE
General ordering information	
EAN13 code	8015747028431
Tariff number	85369095
Packaging Information	
Packaging length	330,00 mm
Packaging height	170,00 mm
Packaging width	230,00 mm
Packaging weight	2,00 kg
Packaging volume	12,90 dm ³
Packaging description	Carton box
Packaging quantity	100 Pcs
Packaging EAN code	8015747028448
Sub-packaging length	100,00 mm
Sub-packaging height	58,00 mm
Sub-packaging width	145,00 mm
Sub-packaging weight	0,20 kg
Sub-packaging volume	0,84 dm ³
Sub-packaging description	Carton Box
Sub-packaging quantity	10 Pcs
Sub-packaging EAN barcode	8015747028455