

Part number

CMAV 03 G29



Brief description:

hoods with two levers, size "57.27" insulated 830V, top entry, Pg29, insulated 830V version, IP66 (EN 60529) and IP69K (DIN 40050 - 9) degree of protection.

Product description

Version	insulated 830V version
Series	Hoods with 2 levers
Product type	with 2 levers
Variant	top entry
Style	high construction
Family	830V enclosures for CME inserts
Size	size "57.27" insulated 830V

Technical data

Material	metal
IP degree of protection	IP66 (and IP69K DIN 40050 - 9)
Cable entry	Pg29

Further technical details

Weight	302,00 g
---------------	----------

Approvals / Standards

Quality mark	 (type:4/4X/12),  , EAC
Conformity	CQC, CE

General ordering information

EAN13 code	8015747029667
Tariff number	85369095

Packaging Information

Sub-packaging weight	0,30 kg
Sub-packaging description	Plastic packaging
Sub-packaging quantity	1 Pcs
Sub-packaging EAN barcode	8015747122092