

Part number

# COB 10 CMS



## Brief description:

insert carrier insulated housings for mobile mounting, side entry, with cable clamp for insert coupling with screw fixing centre distance of 57 x 27 mm

Product description	
Version	COB panel supports for multipole connectors
Series	COB panel supports for multipole connectors
Product type	insert carrier insulated housings for mobile mounting
Style	side entry, with cable clamp for insert coupling with screw fixing centre distance of 57 x 27 mm
Family	accessories for multipole connectors
Size	size "57.27"
Technical data	
Operating temperature range (min, max)	-40°C ... +125°C
Further technical details	
Weight	70,00 g

Approvals / Standards	
Quality mark	, EAC
Conformity	
General ordering information	
EAN13 code	8015747036559
Tariff number	85369095
Packaging Information	
Packaging length	125,00 mm
Packaging height	110,00 mm
Packaging width	225,00 mm
Packaging weight	0,70 kg
Packaging volume	3,09 dm <sup>3</sup>
Packaging description	Carton box
Packaging quantity	10 Pcs
Packaging EAN code	8015747036566
Sub-packaging weight	0,07 kg
Sub-packaging description	Carton
Sub-packaging quantity	1 Pcs
Sub-packaging EAN barcode	8015747036573

Part number

# COB 10 CMS



Catalogue drawings

**COB..CMS**

