

Part number

# CQEEF 40



## Brief description:

female insert, 40 poles + PE, crimp connections, 16A 500V, 6kV, 3, size "77.27", CLASS insert series

Product description		Approvals / Standards	
<b>Model</b>	female insert	<b>Reference standard</b>	EN 61984 (2001-11)
<b>Version</b>	crimp connections	<b>Quality mark</b>	UL, EAC
<b>Series</b>	CQEE	<b>Conformity</b>	CQC, CE
<b>Product type</b>	for female contacts 16A	<b>General ordering information</b>	
<b>Family</b>	CLASS inserts	<b>EAN13 code</b>	8015747200431
<b>Size</b>	size "77.27"	<b>Tariff number</b>	85369095
<b>N. of poles</b>	40 poles +	<b>Country of origin</b>	Made in EU (IT)
<b>Technical data</b>		<b>ETIM classification</b>	EC000438
<b>Current</b>	16 A (A.C. and D.C.)	<b>Packaging Information</b>	
<b>Voltage</b>	500 V	<b>Packaging length</b>	210,00 mm
<b>Rated impulse withstand voltage</b>	6kV	<b>Packaging height</b>	130,00 mm
<b>Pollution degree</b>	3	<b>Packaging width</b>	240,00 mm
<b>Operating temperature range (min, max)</b>	-40°C ... +125°C	<b>Packaging weight</b>	2,43 kg
<b>Mating cycles</b>	≥ 500	<b>Packaging volume</b>	6,55 dm <sup>3</sup>
<b>IP degree of protection</b>	IP20 without enclosure; IP65/IP66/IP67/IP68 with enclosure	<b>Packaging description</b>	Carton box
<b>PE wire cross-section</b>	0,14 - 4 mm <sup>2</sup> ; AWG 20 - 12	<b>Packaging quantity</b>	30 Pcs
<b>Further technical details</b>		<b>Packaging EAN code</b>	8015747200509
<b>Characteristics according to EN 61984</b>	16A 500V 6kV 3	<b>Sub-packaging weight</b>	0,41 kg
<b>Insulation resistance</b>	≥ 10 GΩ	<b>Sub-packaging description</b>	Carton
<b>Rated voltage according to UL/CSA</b>	600V	<b>Sub-packaging quantity</b>	5 Pcs
<b>UL 94 flammability rating</b>	V-0	<b>Sub-packaging EAN barcode</b>	8015747200448
<b>Weight</b>	68,00 g		