


Part number

# CX 1.6 VC



## Brief description:

Pneumatic contacts, with closing valve, for tubes with internal Ø 1,6 mm;

Product description		Approvals / Standards	
<b>Model</b>	pneumatic female contacts	<b>Quality mark</b>	 , EAC
<b>Series</b>	for tubes with internal Ø 1,6 mm	<b>Conformity</b>	
<b>Variant</b>	with closing valve	<b>General ordering information</b>	
<b>Family</b>	Pneumatic contacts	<b>EAN13 code</b>	8015747042024
Technical data		<b>Packaging Information</b>	
<b>Operating temperature range (min, max)</b>	-40°C ... +125°C	<b>Sub-packaging description</b>	Plastic bag
Further technical details		<b>Sub-packaging quantity</b>	3 Pcs
<b>Weight</b>	1,00 g	<b>Sub-packaging EAN barcode</b>	8015747042031

Part number

**CX 1.6 VC**



Catalogue drawings

