

Part number

# CX7FA 25



## Brief description:

70A CX contacts, silver plated, 25mmq, AWG 4 - 3

### Product description

<b>Model</b>	female contacts
<b>Version</b>	Crimp contacts CLASS series
<b>Series</b>	70A CX contacts
<b>Family</b>	crimp contacts
<b>N. of poles</b>	1 pole

### Technical data

<b>Current</b>	70 A
<b>Wire cross-section</b>	25,00 mm <sup>2</sup>
<b>AWG size</b>	4 - 3
<b>Operating temperature range (min, max)</b>	-40°C ... +125°C
<b>Contact type</b>	silver plated

### Further technical details

<b>Weight</b>	9,00 g
---------------	--------

### Approvals / Standards

<b>Quality mark</b>	, EAC
---------------------	-------

### General ordering information

<b>EAN13 code</b>	8015747182515
<b>Tariff number</b>	85369095

### Packaging Information

<b>Sub-packaging length</b>	50,00 mm
<b>Sub-packaging height</b>	44,00 mm
<b>Sub-packaging width</b>	50,00 mm
<b>Sub-packaging weight</b>	0,14 kg
<b>Sub-packaging volume</b>	0,11 dm <sup>3</sup>
<b>Sub-packaging description</b>	Plastic box
<b>Sub-packaging quantity</b>	16 Pcs
<b>Sub-packaging EAN barcode</b>	8015747182591

Part number

**CX7FA 25**



Catalogue drawings

