

Part number

CX7MA 16



Brief description:

70A CX contacts, silver plated, 16mmq, AWG 6 - 5

Product description

Model	male contacts
Version	Crimp contacts CLASS series
Series	70A CX contacts
Family	crimp contacts
N. of poles	1 pole

Technical data

Current	70 A
Wire cross-section	16,00 mm ²
AWG size	6 - 5
Operating temperature range (min, max)	-40°C ... +125°C
Contact type	silver plated

Further technical details

Weight	10,00 g
---------------	---------

Approvals / Standards

Quality mark	UL, EAC
---------------------	---------

General ordering information

EAN13 code	8015747182478
Tariff number	85369095

Packaging Information

Sub-packaging length	50,00 mm
Sub-packaging height	44,00 mm
Sub-packaging width	50,00 mm
Sub-packaging weight	0,16 kg
Sub-packaging volume	0,11 dm ³
Sub-packaging description	Plastic box
Sub-packaging quantity	16 Pcs
Sub-packaging EAN barcode	8015747182553

Part number

CX7MA 16



Catalogue drawings

