

Part number

# CXFA 4.0



## Brief description:

40A CX contacts, silver plated, 4mmq, AWG 12

### Product description

<b>Model</b>	female contacts
<b>Version</b>	Crimp contacts CLASS series
<b>Series</b>	40A CX contacts
<b>Family</b>	crimp contacts
<b>N. of poles</b>	1 pole

### Technical data

<b>Current</b>	40 A
<b>Wire cross-section</b>	4,00 mm <sup>2</sup>
<b>AWG size</b>	12
<b>Contact type</b>	silver plated

### Further technical details

<b>Weight</b>	2,93 g
---------------	--------

### Approvals / Standards

<b>Quality mark</b>	, EAC
<b>Conformity</b>	CQC, CE

### General ordering information

<b>EAN13 code</b>	8015747042499
<b>Tariff number</b>	85369095

### Packaging Information

<b>Packaging length</b>	112,00 mm
<b>Packaging height</b>	95,00 mm
<b>Packaging width</b>	117,00 mm
<b>Packaging weight</b>	1,17 kg
<b>Packaging volume</b>	1,24 dm <sup>3</sup>
<b>Packaging description</b>	Carton box
<b>Packaging quantity</b>	400 Pcs
<b>Packaging EAN code</b>	8015747207058
<b>Sub-packaging length</b>	50,00 mm
<b>Sub-packaging height</b>	44,00 mm
<b>Sub-packaging width</b>	50,00 mm
<b>Sub-packaging weight</b>	0,15 kg
<b>Sub-packaging volume</b>	0,11 dm <sup>3</sup>
<b>Sub-packaging description</b>	Plastic box
<b>Sub-packaging quantity</b>	50 Pcs
<b>Sub-packaging EAN barcode</b>	8015747042505

Part number

# CXFA 4.0



Catalogue drawings

**CXF CXM**

