

Part number

CXFA 6.0



Brief description:

40A CX contacts, silver plated, 6mmq, AWG 10

Product description

Model	female contacts
Version	Crimp contacts CLASS series
Series	40A CX contacts
Family	crimp contacts
N. of poles	1 pole

Technical data

Current	40 A
Wire cross-section	6,00 mm ²
AWG size	10
Contact type	silver plated

Further technical details

Weight	3,20 g
---------------	--------

Approvals / Standards

Quality mark	, EAC
Conformity	CQC, CE

General ordering information

EAN13 code	8015747042512
Tariff number	85369095

Packaging Information

Packaging length	112,00 mm
Packaging height	95,00 mm
Packaging width	117,00 mm
Packaging weight	1,28 kg
Packaging volume	1,24 dm ³
Packaging description	Carton box
Packaging quantity	400 Pcs
Packaging EAN code	8015747207065
Sub-packaging length	50,00 mm
Sub-packaging height	44,00 mm
Sub-packaging width	50,00 mm
Sub-packaging weight	0,16 kg
Sub-packaging volume	0,11 dm ³
Sub-packaging description	Plastic box
Sub-packaging quantity	50 Pcs
Sub-packaging EAN barcode	8015747042529

Part number

CXFA 6.0



Catalogue drawings

CXF CXM

