

Part number

CZAP 25 L



Brief description:

surface mounting housings with single lever, size "66.16", Pg16, metal version, IP66

Product description		Approvals / Standards	
Version	CZ levers, standard version	Quality mark	 (type:4/4X/12),  , EAC
Series	Surface mounting housings with single lever	Conformity	CQC, CE
Product type	with 1 lever	General ordering information	
Family	CZ - MZ enclosures	EAN13 code	8015747043335
Size	size "66.16"	Tariff number	85369095
Technical data		Packaging Information	
Operating temperature range (min, max)	-40°C ... +125°C	Packaging length	270,00 mm
Material	metal	Packaging height	130,00 mm
IP degree of protection	IP66 (and IP69K DIN 40050 - 9)	Packaging width	135,00 mm
Cable entry	Pg16	Packaging weight	2,00 kg
Further technical details		Packaging volume	4,74 dm³
Weight	200,00 g	Packaging description	Carton box
		Packaging quantity	10 Pcs
		Packaging EAN code	8015747258050
		Sub-packaging weight	1,00 kg
		Sub-packaging description	Plastic packaging
		Sub-packaging quantity	5 Pcs
		Sub-packaging EAN barcode	8015747258067