

Part number

# CZV 25 L



## Brief description:

hoods for single lever, size "66.16", top entry, Pg16, metal version, IP66

### Product description

Version	CZ levers, standard version
Series	Hoods with 2 pegs
Product type	with 2 pegs
Variant	top entry
Family	CZ - MZ enclosures
Size	size "66.16"

### Technical data

Operating temperature range (min, max)	-40°C ... +125°C
Material	metal
IP degree of protection	IP66 (and IP69K DIN 40050 - 9)
Cable entry	Pg16

### Further technical details

Weight	100,00 g
--------	----------

### Approvals / Standards

Quality mark	 (type:4/4X/12),  , EAC
Conformity	CQC, CE

### General ordering information

EAN13 code	8015747044929
Tariff number	85369095

### Packaging Information

Packaging length	210,00 mm
Packaging height	130,00 mm
Packaging width	240,00 mm
Packaging weight	2,05 kg
Packaging volume	6,55 dm <sup>3</sup>
Packaging description	Carton box
Packaging quantity	20 Pcs
Packaging EAN code	8015747207485
Sub-packaging weight	0,51 kg
Sub-packaging description	Plastic packaging
Sub-packaging quantity	5 Pcs
Sub-packaging EAN barcode	8015747191906


Part number

**CZV 25 L**




# Catalogue drawings


## CZO L - MZO L



## CZAO L MZAO L - CZAV L MZAV L



## CZV L - MZV L



## MZFO - MZFV L

