

Part number

CZV 25 LG



Brief description:

hoods for single lever, size "66.16", top entry, Pg16, metal version, IP66

Product description		Approvals / Standards	
Version	CZ levers, standard version	Quality mark	 (type:4/4X/12),  , EAC
Series	Hoods with 1 lever	Conformity	CQC, CE
Product type	with 1 lever	General ordering information	
Variant	top entry	EAN13 code	8015747044943
Family	CZ - MZ enclosures	Tariff number	85369095
Size	size "66.16"	Packaging Information	
Technical data		Packaging length	170,00 mm
Operating temperature range (min, max)	-40°C ... +125°C	Packaging height	105,00 mm
Material	metal	Packaging width	270,00 mm
IP degree of protection	IP66 (and IP69K DIN 40050 - 9)	Packaging weight	1,30 kg
Cable entry	Pg16	Packaging volume	4,82 dm³
Further technical details		Packaging description	Carton box
Weight	130,00 g	Packaging quantity	10 Pcs
		Packaging EAN code	8015747044950
		Sub-packaging weight	0,65 kg
		Sub-packaging description	Plastic packaging
		Sub-packaging quantity	5 Pcs
		Sub-packaging EAN barcode	8015747217675

Part number

CZV 25 LG



Catalogue drawings

CZV LG MZV LG

