

Part number

MAO 10 YX32



Brief description:

hoods with central lever, size "57.27", side entry, M32, single lever central position version, IP66

Product description

Version	single lever central position version
Series	hoods with central lever
Product type	with central lever
Variant	side entry
Family	Central lever enclosures YC/YX
Size	size "57.27"

Technical data

Material	metal
IP degree of protection	IP66 (and IP69K DIN 40050 - 9)
Cable entry	M32

Further technical details

Weight	297,00 g
---------------	----------

Approvals / Standards

Quality mark	UL (type:4/4X/12), CE, EAC
Conformity	CQC, CE

General ordering information

EAN13 code	8015747151610
Tariff number	85369095

Packaging Information

Packaging length	290,00 mm
Packaging height	130,00 mm
Packaging width	210,00 mm
Packaging weight	3,20 kg
Packaging volume	7,92 dm ³
Packaging description	Carton box
Packaging quantity	10 Pcs
Packaging EAN code	8015747215015
Sub-packaging weight	1,60 kg
Sub-packaging description	Plastic packaging
Sub-packaging quantity	5 Pcs
Sub-packaging EAN barcode	8015747088046

Part number

MAO 10 YX32



Catalogue drawings

CAO.YX - MAO.YX

