

Part number

MAV 06 L25



Brief description:

hoods for single lever, size "44.27", top entry, M25, metal version, IP66



Product description

Version	metal version
Series	hoods for single lever
Product type	with 2 pegs
Variant	top entry
Style	high construction
Family	CLASS enclosures
Size	size "44.27"

Technical data

Material	metal
IP degree of protection	IP66 (and IP69K DIN 40050 - 9)
Cable entry	M25

Further technical details

Weight	168,00 g
---------------	----------

Approvals / Standards

Quality mark	UL [®] (type:4/4X/12), [®] , EAC
Conformity	CQC, CE

General ordering information

EAN13 code	8015747052078
Tariff number	85369095

Packaging Information

Sub-packaging weight	0,84 kg
Sub-packaging description	Plastic packaging
Sub-packaging quantity	5 Pcs
Sub-packaging EAN barcode	8015747052085


Part number

MAV 06 L25




Catalogue drawings

CHO LX CHV LX - MHO LX MHV LX



CHV LG (CAV LG), MHV LG (MAV LG) [MFV LG]



CHO L (CAO L) - MHO (MAO/MFO/MFV L) MHV L [MAV L]

