

Part number

MZP 15 L25



Brief description:

surface mounting housings with single lever, size "49.16", M25, metal version, IP66

Product description		Approvals / Standards	
Version	CZ levers, standard version	Quality mark	 (type:4/4X/12),  , EAC
Series	Surface mounting housings with single lever	Conformity	CQC, CE
Product type	with 1 lever	General ordering information	
Family	CZ - MZ enclosures	EAN13 code	8015747060493
Size	size "49.16"	Tariff number	85369095
Technical data		Packaging Information	
Operating temperature range (min, max)	-40°C ... +125°C	Packaging length	140,00 mm
Material	metal	Packaging height	120,00 mm
IP degree of protection	IP66 (and IP69K DIN 40050 - 9)	Packaging width	260,00 mm
Cable entry	M25	Packaging weight	1,70 kg
Further technical details		Packaging volume	4,37 dm ³
Weight	170,00 g	Packaging description	Carton box
		Packaging quantity	10 Pcs
		Packaging EAN code	8015747171939
		Sub-packaging weight	0,85 kg
		Sub-packaging description	Plastic packaging
		Sub-packaging quantity	5 Pcs
		Sub-packaging EAN barcode	8015747171946