

Part number

# TCHC 06 LG



#### Product description

<b>Version</b>	T-TYPE insulating enclosures
<b>Series</b>	Covers with levers
<b>Product type</b>	with one lever in thermoplastic material
<b>Family</b>	T-TYPE insulating enclosures
<b>Size</b>	size "44.27", covers

#### Technical data

<b>Operating temperature range (min, max)</b>	-40°C ... +90°C
<b>Material</b>	thermoplastic
<b>IP degree of protection</b>	IP65

#### Further technical details

<b>Weight</b>	42,00 g
---------------	---------

#### Approvals / Standards

<b>Quality mark</b>	 (type:12), EAC
<b>Conformity</b>	CQC, CE

#### General ordering information

<b>EAN13 code</b>	8015747209205
<b>Tariff number</b>	85369095

#### Packaging Information

<b>Packaging length</b>	325,00 mm
<b>Packaging height</b>	180,00 mm
<b>Packaging width</b>	180,00 mm
<b>Packaging weight</b>	0,84 kg
<b>Packaging volume</b>	10,53 dm <sup>3</sup>
<b>Packaging description</b>	Carton box
<b>Packaging quantity</b>	20 Pcs
<b>Packaging EAN code</b>	8015747209243
<b>Sub-packaging weight</b>	0,04 kg
<b>Sub-packaging description</b>	Plastic bag
<b>Sub-packaging quantity</b>	1 Pcs
<b>Sub-packaging EAN barcode</b>	8015747209250