

Part number
TCHC 10



Brief description:

covers, size "57.27", thermoplastic version, IP65



Product description

Version	T-TYPE insulating enclosures
Series	Covers with pegs
Product type	with 4 pegs
Family	T-TYPE insulating enclosures
Size	size "57.27", covers

Technical data

Operating temperature range (min, max)	-40°C ... +90°C
Material	thermoplastic
IP degree of protection	IP65

Further technical details

Weight	32,00 g
---------------	---------

Approvals / Standards

Quality mark	UL [®] (type:12), EAC
Conformity	CQC, CE

General ordering information

EAN13 code	8015747168823
Tariff number	85369095

Packaging Information

Packaging length	210,00 mm
Packaging height	130,00 mm
Packaging width	240,00 mm
Packaging weight	0,64 kg
Packaging volume	6,55 dm ³
Packaging description	Carton box
Packaging quantity	20 Pcs
Packaging EAN code	8015747229289
Sub-packaging weight	0,03 kg
Sub-packaging description	Plastic bag
Sub-packaging quantity	1 Pcs
Sub-packaging EAN barcode	8015747227735

Part number

TCHC 10



Catalogue drawings

