


Part number

TCHC 16 G



Product description		Approvals / Standards	
Version	T-TYPE insulating enclosures	Quality mark	 (type:12), EAC
Series	Covers with levers	Conformity	CQC, CE
Product type	with two levers in thermoplastic material	General ordering information	
Family	T-TYPE insulating enclosures	EAN13 code	8015747209229
Size	size "77.27", covers	Tariff number	85369095
Technical data		Packaging Information	
Operating temperature range (min, max)	-40°C ... +90°C	Packaging length	325,00 mm
Material	thermoplastic	Packaging height	180,00 mm
IP degree of protection	IP65	Packaging width	180,00 mm
Further technical details		Packaging weight	0,92 kg
Weight	46,00 g	Packaging volume	10,53 dm ³
		Packaging description	Carton box
		Packaging quantity	20 Pcs
		Packaging EAN code	8015747209281
		Sub-packaging weight	0,05 kg
		Sub-packaging description	Plastic bag
		Sub-packaging quantity	1 Pcs
		Sub-packaging EAN barcode	8015747209298