


Part number
THIH 10



Brief description:

bulkhead mounting housings with 2 levers, size "57.27", HYGENIC enclosures T-TYPE /H version, IP66 and IP69

| Product description | |
|--|---|
| Version | HYGENIC enclosures T-TYPE /H version |
| Series | Bulkhead mounting housings with 2 levers |
| Product type | with two levers in thermoplastic material |
| Family | T-TYPE insulating enclosures |
| Size | size "57.27" |
| Technical data | |
| Operating temperature range (min, max) | -40°C ... +70°C |
| Material | thermoplastic |
| IP degree of protection | IP66/IP69 |
| Further technical details | |
| Weight | 81,00 g |

| Approvals / Standards | |
|------------------------------|--|
| Quality mark |  (type:12), EAC |
| Conformity | CQC, CE |
| General ordering information | |
| EAN13 code | 8015747209762 |
| Tariff number | 85369095 |
| Packaging Information | |
| Packaging length | 305,00 mm |
| Packaging height | 180,00 mm |
| Packaging width | 275,00 mm |
| Packaging weight | 3,22 kg |
| Packaging volume | 15,10 dm ³ |
| Packaging description | Carton box |
| Packaging quantity | 40 Pcs |
| Packaging EAN code | 8015747209816 |
| Sub-packaging weight | 0,40 kg |
| Sub-packaging description | Plastic pakaging |
| Sub-packaging quantity | 5 Pcs |
| Sub-packaging EAN barcode | 8015747209823 |