


Part number  
**THIH 16**



**Brief description:**

bulkhead mounting housings with 2 levers, size "77.27" , HYGENIC enclosures T-TYPE /H version, IP66 and IP69

Product description	
Version	HYGENIC enclosures T-TYPE /H version
Series	Bulkhead mounting housings with 2 levers
Product type	with two levers in thermoplastic material
Family	T-TYPE insulating enclosures
Size	size "77.27"
Technical data	
Operating temperature range (min, max)	-40°C ... +70°C
Material	thermoplastic
IP degree of protection	IP66/IP69
Further technical details	
Weight	86,00 g

Approvals / Standards	
Quality mark	 (type:12), EAC
Conformity	CQC, CE
General ordering information	
EAN13 code	8015747209779
Tariff number	85369095
Packaging Information	
Packaging length	360,00 mm
Packaging height	170,00 mm
Packaging width	305,00 mm
Packaging weight	3,47 kg
Packaging volume	18,67 dm <sup>3</sup>
Packaging description	Carton box
Packaging quantity	40 Pcs
Packaging EAN code	8015747209830
Sub-packaging weight	0,43 kg
Sub-packaging description	Plastic pakaging
Sub-packaging quantity	5 Pcs
Sub-packaging EAN barcode	8015747209847