


Part number

# TMAO 06 L25



## Brief description:

hoods for single lever, size "44.27", side entry, M25, thermoplastic version, IP65

Product description		Approvals / Standards	
Version	T-TYPE insulating enclosures	Quality mark	 (type:12), EAC
Series	Hoods with 2 pegs	Conformity	CQC, CE
Product type	with 2 pegs	General ordering information	
Variant	side entry	EAN13 code	8015747168656
Family	T-TYPE insulating enclosures	Tariff number	85369095
Size	size "44.27"	Packaging Information	
Technical data		Packaging length	255,00 mm
Operating temperature range (min, max)	-40°C ... +90°C	Packaging height	150,00 mm
Material	thermoplastic	Packaging width	180,00 mm
IP degree of protection	IP65	Packaging weight	2,12 kg
Cable entry	M25	Packaging volume	6,89 dm <sup>3</sup>
Further technical details		Packaging description	Carton box
Weight	106,00 g	Packaging quantity	20 Pcs
		Packaging EAN code	8015747171083
		Sub-packaging weight	0,53 kg
		Sub-packaging description	Plastic pakaging
		Sub-packaging quantity	5 Pcs
		Sub-packaging EAN barcode	8015747171090

Part number

# TMAO 06 L25



Catalogue drawings

