

Part number


# TMAO 10.25



## Brief description:

hoods for two levers, size "57.27", side entry, M25, thermoplastic version, IP65

| Product description                    |                              |
|--|------------------------------|
| Version                                | T-TYPE insulating enclosures |
| Series                                 | Hoods with 4 pegs            |
| Product type                           | with 4 pegs                  |
| Variant                                | side entry                   |
| Family                                 | T-TYPE insulating enclosures |
| Size                                   | size "57.27"                 |
| Technical data                         |                              |
| Operating temperature range (min, max) | -40°C ... +90°C              |
| Material                               | thermoplastic                |
| IP degree of protection                | IP65                         |
| Cable entry                            | M25                          |
| Further technical details              |                              |
| Weight                                 | 119,00 g                     |

| Approvals / Standards        |  |
|------------------------------|--|
| Quality mark                 |  (type:12), EAC |
| Conformity                   | CQC, CE  |
| General ordering information |  |
| EAN13 code                   | 8015747168670  |
| Tariff number                | 85369095   |
| Packaging Information        |  |
| Packaging length             | 280,00 mm  |
| Packaging height             | 170,00 mm  |
| Packaging width              | 185,00 mm  |
| Packaging weight             | 2,37 kg  |
| Packaging volume             | 8,81 dm <sup>3</sup>   |
| Packaging description        | Carton box   |
| Packaging quantity           | 20 Pcs   |
| Packaging EAN code           | 8015747171120  |
| Sub-packaging weight         | 0,59 kg  |
| Sub-packaging description    | Plastic pakaging   |
| Sub-packaging quantity       | 5 Pcs  |
| Sub-packaging EAN barcode    | 8015747171137  |

Part number

# TMAO 10.25



Catalogue drawings

