


Part number

TMAO 16.40



Brief description:

hoods for two levers, size "77.27" , side entry, M40, thermoplastic version, IP65

Product description		Approvals / Standards	
Version	T-TYPE insulating enclosures	Quality mark	 (type:12), EAC
Series	Hoods with 4 pegs	Conformity	CQC, CE
Product type	with 4 pegs	General ordering information	
Variant	side entry	EAN13 code	8015747168700
Family	T-TYPE insulating enclosures	Tariff number	85369095
Size	size "77.27"	Packaging Information	
Technical data		Packaging length	280,00 mm
Operating temperature range (min, max)	-40°C ... +90°C	Packaging height	180,00 mm
Material	thermoplastic	Packaging width	230,00 mm
IP degree of protection	IP65	Packaging weight	2,34 kg
Cable entry	M40	Packaging volume	11,59 dm ³
Further technical details		Packaging description	Carton box
Weight	117,00 g	Packaging quantity	20 Pcs
		Packaging EAN code	8015747171182
		Sub-packaging weight	0,59 kg
		Sub-packaging description	Plastic pakaging
		Sub-packaging quantity	5 Pcs
		Sub-packaging EAN barcode	8015747171199

Part number

TMAO 16.40



Catalogue drawings

