


Part number

# TMAO 24.32



## Brief description:

hoods for two levers, size "104.27" , side entry, M32, thermoplastic version, IP65

Product description		Approvals / Standards	
Version	T-TYPE insulating enclosures	Quality mark	 (type:12), EAC
Series	Hoods with 4 pegs	Conformity	CQC, CE
Product type	with 4 pegs	<b>General ordering information</b>	
Variant	side entry	EAN13 code	8015747168724
Family	T-TYPE insulating enclosures	Tariff number	85369095
Size	size "104.27"	<b>Packaging Information</b>	
<b>Technical data</b>		Packaging length	290,00 mm
Operating temperature range (min, max)	-40°C ... +90°C	Packaging height	185,00 mm
Material	thermoplastic	Packaging width	280,00 mm
IP degree of protection	IP65	Packaging weight	3,39 kg
Cable entry	M32	Packaging volume	15,02 dm <sup>3</sup>
<b>Further technical details</b>		Packaging description	Carton box
Weight	170,00 g	Packaging quantity	20 Pcs
		Packaging EAN code	8015747171229
		Sub-packaging weight	0,85 kg
		Sub-packaging description	Plastic pakaging
		Sub-packaging quantity	5 Pcs
		Sub-packaging EAN barcode	8015747171236