

Part number

# TMAV 10.32



## Brief description:

hoods for two levers, size "57.27", top entry, M32, thermoplastic version, IP65

### Product description

Version	T-TYPE insulating enclosures
Series	Hoods with 4 pegs
Product type	with 4 pegs
Variant	top entry
Family	T-TYPE insulating enclosures
Size	size "57.27"

### Technical data

Operating temperature range (min, max)	-40°C ... +90°C
Material	thermoplastic
IP degree of protection	IP65
Cable entry	M32

### Further technical details

Weight	102,00 g
--------	----------

### Approvals / Standards

Quality mark	 (type:12), EAC
Conformity	CQC, CE

### General ordering information

EAN13 code	8015747168762
Tariff number	85369095

### Packaging Information

Packaging length	270,00 mm
Packaging height	210,00 mm
Packaging width	165,00 mm
Packaging weight	2,04 kg
Packaging volume	9,36 dm <sup>3</sup>
Packaging description	Carton box
Packaging quantity	20 Pcs
Packaging EAN code	8015747171304
Sub-packaging weight	0,51 kg
Sub-packaging description	Plastic pakaging
Sub-packaging quantity	5 Pcs
Sub-packaging EAN barcode	8015747171311

Part number

# TMAV 10.32



Catalogue drawings

