


# KTF

## Grommets for KEL-JUMBO



Type	Order No. gray	Clamping range	PU
KTF 00	42371	Blank grommet	1
KTA	42370	Adapter grommet for KT large	1
KTF 34	42376	33 - 36 mm	1
KTF 38	42379	37 - 40 mm	1
KTF 42	42382	41 - 44 mm	1
KTF 46	42385	45 - 48 mm	1
KTF 50	42388	48 - 52 mm	1
KTF 54	42391	53 - 56 mm	1
KTF 58	42394	56 - 60 mm	1
KTF 62	42397	61 - 65 mm	1

### Product Description

The grommets KTF are suitable for cable diameters up to 65 mm.

Suitable for KEL-JUMBO cable entry frames.

Cables with a comparatively smaller diameter can be utilized with KEL-JUMBO frames by using an adapter grommet.

### Specifications

Material	Elastomer
Flame class	UL94-Vo
IP rating	IP54
NEMA type rating	NEMA type 12 (acc. to UL 50E)
Temperature	- 40°C to + 90°C (static) - 40°F to + 194°F (static)
Properties	Halogen-free, silicone-free

### Compatible with

KEL-JUMBO Cable entry frames 34

### Accessories

KT Cable grommets, large 46