

BPM

Metal Blank Plates



Type	Order No.	Blank plate for KEL cut-out	Dimensions	PU
BPM-B	42013	KEL-B KEL-U-B KEL-QUICK-B	75 × 58 mm	10
BPM 6 BPM 6 V2A	42011 41991	standard 6-pole industrial connectors	90 × 52 mm	10
BPM 10 BPM 10 V2A	42014 41992	KEL 10 KEL-U 10	99 × 58 mm	10
BPM-FG B	42012	KEL-FG B	80 × 58 mm	10
BPM 16 BPM 16 V2A	42025 41994	KEL 16 KEL-U 16 KEL-QUICK 16	118 × 56 mm	10
BPM 16-E	42023	KEL 16-E	120 × 87 mm	10
BPM 16-MT	42026	KEL 16-MT	120 × 102 mm	10
BPM 16-2MT	42031	KEL 16-2MT	120 × 146 mm	10
BPM 24 BPM 24 V2A	42027 41995	KEL 24 KEL-U 24 KEL-QUICK 24	145 × 56 mm	10
BPM 24-E	42029	KEL 24-E	143 × 83 mm	10
BPM 24-MT	42028	KEL 24-MT	147 × 102 mm	1
BPM-JUMBO flex	42033	KEL-JUMBO flex	88 × 88 mm	1
BPM-JUMBO 1	42030	KEL-JUMBO 1	116 × 110 mm	1
BPM-JUMBO 2	42032	KEL-JUMBO 2	200 × 116 mm	1
BPM-ULTRA	42633	KEL-ULTRA flex	∅ 168 mm Width: 1,5 mm	1

Product Description

Blank plates to close cut-outs for standard 6-pole / 10-pole / 16-pole / 24-pole industrial connectors.

Blank plates are supplied with a gasket.

Specifications

Material	Carbon steel, zinc-plated
	Width 2 mm
IP rating	IP54

Compatible with

KDR 2 Split base plates	144 - 145
FP Flanged plates	152 - 157
MP Module plates	148 - 149