



## CONFiX SH

### Conduit Clips for WST



Type	Order No.	Suitable conduit	Fixing hole	Width [mm]	Height [mm]	PU
CONFiX SH 10	31300	NW 10	M3	18.5	21	10
CONFiX SH 14	31310	NW 14	M3	24	25.5	10
CONFiX SH 20	31320	NW 20	M5	35	36	10
CONFiX SH 23	31330	NW 23	M5	42	43.5	10
CONFiX SH 37	31340	NW 37	M6	55	56.5	10
CONFiX SH 45	31350	NW 45	M6	67	68	10
CONFiX SH 70	31360	NW 70	M6	100	101	10

### Product Description

CONFiX SH Conduit clips are a one-piece clamping system to provide secure mounting points for corrugated conduit systems.

The clips are secured to their mounting position through a central mounting point with a hexagonal counter-bore.

### Specifications

Material Polyamide (PA), black  
 Flame class UL94-V2  
 Temperature - 40°C to + 140°C  
 Properties Halogen free, silicone free

### Compatible with

CONFiX WST  
 Split corrugated conduit 138