



V2A  
anti-corrosive

Also available with stainless steel screws (V2A).



IP54

Type	Order No.	Cut-out	Grommets KTF	PU
KEL-JUMBO 1 ATEX	49506	78 × 80.5 mm	1	1
KEL-JUMBO 1 ATEX with V2A screws	49506.200	78 × 80.5 mm	1	1
KEL-JUMBO 2 ATEX	49507	168 × 80.5 mm	2	1
KEL-JUMBO 2 ATEX with V2A screws	49507.200	168 × 80.5 mm	2	1

## Product Description

The KEL-JUMBO cable entry system for installation of cables and conduits with a diameter of up to 65 mm, especially suited for supply cables.

The innovative grommet design with the flex-membrane provides flexing and adjustment of the position for larger and more rigid cables.

We recommend round cut-outs, which can be made using standard punching tools.

Suggested cut-out: cable diameter +15 - 20%.  
A flat rubber gasket is included in the shipment.

## Advantages & Benefits

- Installation of cables up to 65 mm
- KTF grommets allow flexing and adjustment of the cable position
- Retrofitting and maintenance can be carried out easily and quickly

## Specifications

Material	Polyamide (PA)
Flame class	UL94-Vo
IP rating	IP54, with gasket and correct selection of cable grommets
NEMA type rating	NEMA type 12 (acc. to UL 50E)
Temperature	- 30°C to + 90°C (static) - 22°F to + 194°F (static)
Equipment group	II
Category	2G, 3G, 2D, 3D
Zone	1 + 21, 2+22
Test standard	EN 60079-0
Properties	Halogen-free, silicone-free
Frame depth	35 mm

## Accessories

KTF Cable grommets 35