

PFSZ2|SKL

EMC Double Shield Clamps for Bus Bar



Product Description

Comparable with the PFS2|SKL range, the PFSZ2|SKL shield clamps are easy to use and effective in grounding 2 single cables. They are used for mounting on 10 × 3 mm bus bars.

The PFSZ2 range provides possibility to fix the cables with cable ties. Strain relief in accordance with EN 62444 is achieved.

Advantages & Benefits

- Integrated strain relief
- Large contact area
- Simple and tool-free mounting, easy assembly
- The spring design requires no adjustments and will permanently maintain contact to the cable shield
- Shock and vibration resistant, maintenance free

Specifications

Material

SKL-clamp **Spring steel, zinc plated**
PFSZ2-foot **Spring steel**
Bus bar **Cu, tin plated, max. current: 140 Amps**

Accessories

KB Cable ties 88 - 89

Type	Shield diameter Pos. 1	Shield diameter Pos. 2	Order No.	PU
PFSZ2 SKL 01	blank	1.5 - 3 mm	36789.01	10
PFSZ2 SKL 02	blank	3 - 6 mm	36789.02	10
PFSZ2 SKL 03	blank	6 - 8 mm	36789.03	10
PFSZ2 SKL 04	blank	8 - 11 mm	36789.04	10
PFSZ2 SKL 10	1.5 - 3 mm	blank	36789.10	10
PFSZ2 SKL 11	1.5 - 3 mm	1.5 - 3 mm	36789.11	10
PFSZ2 SKL 12	1.5 - 3 mm	3 - 6 mm	36789.12	10
PFSZ2 SKL 13	1.5 - 3 mm	6 - 8 mm	36789.13	10
PFSZ2 SKL 14	1.5 - 3 mm	8 - 11 mm	36789.14	10
PFSZ2 SKL 20	3 - 6 mm	blank	36789.20	10
PFSZ2 SKL 21	3 - 6 mm	1.5 - 3 mm	36789.21	10
PFSZ2 SKL 22	3 - 6 mm	3 - 6 mm	36789.22	10
PFSZ2 SKL 23	3 - 6 mm	6 - 8 mm	36789.23	10
PFSZ2 SKL 24	3 - 6 mm	8 - 11 mm	36789.24	10
PFSZ2 SKL 30	6 - 8 mm	blank	36789.30	10
PFSZ2 SKL 31	6 - 8 mm	1.5 - 3 mm	36789.31	10
PFSZ2 SKL 32	6 - 8 mm	3 - 6 mm	36789.32	10
PFSZ2 SKL 33	6 - 8 mm	6 - 8 mm	36789.33	10
PFSZ2 SKL 34	6 - 8 mm	8 - 11 mm	36789.34	10
PFSZ2 SKL 40	8 - 11 mm	blank	36789.40	10
PFSZ2 SKL 41	8 - 11 mm	1.5 - 3 mm	36789.41	10
PFSZ2 SKL 42	8 - 11 mm	3 - 6 mm	36789.42	10
PFSZ2 SKL 43	8 - 11 mm	6 - 8 mm	36789.43	10
Bus bar 10 × 3 mm		10 × 3 × 1000 mm*	36100	1

* Other lengths available on request