

# AT-B adapter grommets

for custom interface solutions / IP65



AT-B is a blank adapter grommet (based on large KT grommets) for custom interface solutions, suitable for split icotek cable entry systems. The AT-M adapter grommets are made of elastomer with a polyamide body.

The integrated polyamide body is completely closed on one side. The effective area is 24 x 24 mm, the wall thickness is 6 mm. Custom drill-holes and cut-outs can be made here for e.g. installation of screw mounted hybrid connectors.

They are compatible with all split icotek cable entry systems (suitable for KT cable grommets).

IP54

IP55

IP64

IP65

RIWA

HL3  
EN 45545-2

ECOLAB  
certified

UV  
ISO 4892-2A

RoHS  
compliant

REACH  
COMPLIANCE

Made in  
Germany

## Specifications

IP rating (EN 60529)	IP54, IP55, IP64, IP65
Material	Elastomer Body: Polyamide
Flame class	UL94-V0, self-extinguishing
Operating temperature	-40 C° to 100 C°
Properties	silicone free, halogen free

## Advantages & Benefits

- Panel connectors and sockets can be integrated directly into the cable entry system
- Separate cut-outs for connectors are no longer necessary
- Space-saving solution
- Individually usable area is 24 x 24 mm

## Product types & Sizes

AT-B



Part No.	39950
EAN	4251269320934
PU	10
Length	42 mm
Width	41,5 mm
Height	19 mm
Mounting height	2 mm