

KEL-DP multi-membrane cable entry plates

pluggable, with high cable density / IP64 / UL Type 12



KEL-DP entry plates are designed for routing cables without connectors, hoses or fibre optics in limited space.

The KEL-DP products are an easy to assemble and cost saving alternative to traditional cable glands. Simply make a small hole in the thin membrane and push the cables through. The KEL-DP provides protection IP64 / UL type 12.

The KEL-DP matches exactly the cut-out dimensions of 6-, 10-, 16- and 24-pin standard industrial connectors. The very compact size KEL-DP-E is designed for routing cables in very small space. Through a cut-out of only 18 x 112 mm, up to 21 cables can be easily routed and sealed. A special rib ensures a centred fit in the cut-outs.

ST-B Plugs can be used for sealing pierced membranes if cables have been removed.



Specifications

IP rating (EN 60529)	IP54, IP64
UL Type (UL 50E)	UL Type 12
Material	Elastomer
Flame class	UL94-V0, self-extinguishing
Operating temperature	-30 C° to 100 C°
Properties	halogen free, silicone free
Mounting options	Snap-in

Advantages & Benefits

- Quick assembly without tools
- High cable density
- Cost-effective solution
- Hygienic design - free of dirt-collecting recesses

Product types & Sizes

KEL-DP 24|12 A gy



Part No.	43508	Height	12
EAN	4251269309830	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	12	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	12 x 1 - 15 mm
Width	44 mm		

KEL-DP 24|12 A bk

Part No.	50508	Height	12
EAN	4251269314612	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	12	For min. wall thickness	1,5 mm
Color	schwarz	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	12 x 1 - 15 mm
Width	44 mm		

KEL-DP 24|14 A gy

Part No.	43512	Height	12
EAN	4251269309854	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	14	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	14 x 1 - 12.1 mm
Width	44 mm		

KEL-DP 24|14 B gy

Part No.	43522	Height	12
EAN	4251269309939	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	14	For min. wall thickness	2,8 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	4 mm
Length	142 mm	Clamping range	14 x 1 - 12.1 mm
Width	44 mm		

KEL-DP 24|14 A bk

Part No.	50512	Height	12
EAN	4251269314636	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	14	For min. wall thickness	1,5 mm
Color	schwarz	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	14 x 1 - 12.1 mm
Width	44 mm		

KEL-DP 24|14 B bk

Part No.	50522	Height	12
EAN	4251269314711	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	14	For min. wall thickness	2,8 mm
Color	schwarz	For max. wall thickness	4 mm
Length	142 mm	Clamping range	14 x 1 - 12.1 mm
Width	44 mm		

KEL-DP 24|17 A gy

Part No.	43514	Height	12
EAN	4251269309861	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	17	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	5 x 1 - 10.5 mm
Width	44 mm		12 x 1 - 12.6 mm

KEL-DP 24|17 B gy

Part No.	43523	Height	12
EAN	4251269309946	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	17	For min. wall thickness	2,8 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	4 mm
Length	142 mm	Clamping range	5 x 1 - 10.5 mm
Width	44 mm		12 x 1 - 12.6 mm

KEL-DP 24|17 A bk

Part No.	50514	Height	12
EAN	4251269314643	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	17	For min. wall thickness	1,5 mm
Color	schwarz	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	5 x 1 - 10.5 mm
Width	44 mm		12 x 1 - 12.6 mm

KEL-DP 24|17 B bk

Part No.	50523	Height	12
EAN	4251269314728	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	17	For min. wall thickness	2,8 mm
Color	schwarz	For max. wall thickness	4 mm
Length	142 mm	Clamping range	5 x 1 - 10.5 mm
Width	44 mm		12 x 1 - 12.6 mm

KEL-DP 24|18 A gy

Part No.	43515	Height	12
EAN	4251269309878	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	18	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	4 x 1 - 6.5 mm
Width	44 mm		5 x 1 - 10.5 mm
			5 x 1 - 12.6 mm
			4 x 1 - 16.1 mm

KEL-DP 24|18 B gy

Part No.	43528	Height	12
EAN	4251269309991	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	18	For min. wall thickness	2,8 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	4 mm
Length	142 mm	Clamping range	4 x 1 - 6.5 mm
Width	44 mm		5 x 1 - 10.5 mm
			5 x 1 - 12.6 mm
			4 x 1 - 16.1 mm

KEL-DP 24|18 A bk

Part No.	50515	Height	12
EAN	4251269314650	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	18	For min. wall thickness	1,5 mm
Color	schwarz	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	4 x 1 - 6.5 mm
Width	44 mm		5 x 1 - 10.5 mm
			5 x 1 - 12.6 mm
			4 x 1 - 16.1 mm

KEL-DP 24|18 B bk

Part No.	50528	Height	12
EAN	4251269314773	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	18	For min. wall thickness	2,8 mm
Color	schwarz	For max. wall thickness	4 mm
Length	142 mm	Clamping range	4 x 1 - 6.5 mm
Width	44 mm		5 x 1 - 10.5 mm
			5 x 1 - 12.6 mm
			4 x 1 - 16.1 mm

KEL-DP 24|19 A gy

Part No.	43516	Height	12
EAN	4251269309885	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	19	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	12 x 1 - 6.5 mm
Width	44 mm		7 x 1 - 12.1 mm

KEL-DP 24|19 B gy

Part No.	43524	Height	12
EAN	4251269309953	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	19	For min. wall thickness	2,8 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	4 mm
Length	142 mm	Clamping range	12 x 1 - 6.5 mm
Width	44 mm		7 x 1 - 12.1 mm

KEL-DP 24|19 A bk

Part No.	50516	Height	12
EAN	4251269314667	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	19	For min. wall thickness	1,5 mm
Color	schwarz	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	12 x 1 - 6.5 mm
Width	44 mm		7 x 1 - 12.1 mm

KEL-DP 24|19 B bk

Part No.	50524	Height	12
EAN	4251269314735	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	19	For min. wall thickness	2,8 mm
Color	schwarz	For max. wall thickness	4 mm
Length	142 mm	Clamping range	12 x 1 - 6.5 mm
Width	44 mm		7 x 1 - 12.1 mm

KEL-DP 24|26 A gy

Part No.	43518	Height	12
EAN	4251269309892	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	26	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	16 x 1 - 6.5 mm
Width	44 mm		4 x 1 - 12.1 mm

KEL-DP 24|26 B gy

Part No.	43525	Height	12
EAN	4251269309960	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	26	For min. wall thickness	2,8 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	4 mm
Length	142 mm	Clamping range	16 x 1 - 6.5 mm
Width	44 mm		4 x 1 - 12.1 mm
			4 x 1 - 16.1 mm

KEL-DP 24|26 A bk

Part No.	50518	Height	12
EAN	4251269314674	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	26	For min. wall thickness	1,5 mm
Color	schwarz	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	16 x 1 - 6.5 mm
Width	44 mm		4 x 1 - 12.1 mm
			4 x 1 - 16.1 mm

KEL-DP 24|26 B bk

Part No.	50525	Height	12
EAN	4251269314742	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	26	For min. wall thickness	2,8 mm
Color	schwarz	For max. wall thickness	4 mm
Length	142 mm	Clamping range	16 x 1 - 6.5 mm
Width	44 mm		4 x 1 - 12.1 mm
			4 x 1 - 16.1 mm

KEL-DP 24|42 A gy

Part No.	43511	Height	12
EAN	4251269309847	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	42	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	12 x 1 - 7.2 mm
Width	44 mm		17 x 1 - 6.4 mm
			12 x 1 - 5 mm
			1 x 1 - 4.7 mm

KEL-DP 24|42 B gy

Part No.	43521	Height	12
EAN	4251269309922	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	42	For min. wall thickness	2,8 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	4 mm
Length	142 mm	Clamping range	12 x 1 - 7.2 mm
Width	44 mm		17 x 1 - 6.4 mm
			12 x 1 - 5 mm
			1 x 1 - 4.7 mm

KEL-DP 24|42 A bk

Part No.	50511	Height	12
EAN	4251269314629	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	42	For min. wall thickness	1,5 mm
Color	schwarz	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	12 x 1 - 7.2 mm
Width	44 mm		17 x 1 - 6.4 mm
			12 x 1 - 5 mm
			1 x 1 - 4.7 mm

KEL-DP 24|42 B bk

Part No.	50521	Height	12
EAN	4251269314704	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	42	For min. wall thickness	2,8 mm
Color	schwarz	For max. wall thickness	4 mm
Length	142 mm	Clamping range	12 x 1 - 7.2 mm
Width	44 mm		17 x 1 - 6.4 mm
			12 x 1 - 5 mm
			1 x 1 - 4.7 mm

KEL-DP 24|48 A gy

Part No.	43519	Height	12
EAN	4251269309908	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	48	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	48 x 1 - 6.5 mm
Width	44 mm		

KEL-DP 24|48 B gy

Part No.	43526	Height	12
EAN	4251269309977	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	48	For min. wall thickness	2,8 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	4 mm
Length	142 mm	Clamping range	48 x 1 - 6.5 mm
Width	44 mm		

KEL-DP 24|48 A bk

Part No.	50519	Height	12
EAN	4251269314681	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	48	For min. wall thickness	1,5 mm
Color	schwarz	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	48 x 1 - 6.5 mm
Width	44 mm		

KEL-DP 24|48 B bk

Part No.	50526	Height	12
EAN	4251269314759	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	48	For min. wall thickness	2,8 mm
Color	schwarz	For max. wall thickness	4 mm
Length	142 mm	Clamping range	48 x 1 - 6.5 mm
Width	44 mm		

KEL-DP 24|50 A gy

Part No.	43520	Height	12
EAN	4251269309915	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	50	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	33 x 1 - 5.3 mm
Width	44 mm		9 x 1 - 6.4 mm
			8 x 1 - 8.3 mm

KEL-DP 24|50 B gy

Part No.	43527	Height	12
EAN	4251269309984	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	50	For min. wall thickness	2,8 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	4 mm
Length	142 mm	Clamping range	33 x 1 - 5.3 mm
Width	44 mm		9 x 1 - 6.4 mm
			8 x 1 - 8.3 mm

KEL-DP 24|50 A bk

Part No.	50520	Height	12
EAN	4251269314698	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	50	For min. wall thickness	1,5 mm
Color	schwarz	For max. wall thickness	2,5 mm
Length	142 mm	Clamping range	33 x 1 - 5.3 mm
Width	44 mm		9 x 1 - 6.4 mm
			8 x 1 - 8.3 mm

KEL-DP 24|50 B bk

Part No.	50527	Height	12
EAN	4251269314766	Mounting height	5 mm
PU	10	Cut-out size	112 x 36 mm
For max. no. of cables	50	For min. wall thickness	2,8 mm
Color	schwarz	For max. wall thickness	4 mm
Length	142 mm	Clamping range	33 x 1 - 5.3 mm
Width	44 mm		9 x 1 - 6.4 mm
			8 x 1 - 8.3 mm

KEL-DP 16|10 A gy

Part No.	43460	Height	12 mm
EAN	4251269320750	Mounting height	5 mm
PU	10	Cut-out size	86 x 36 mm
For max. no. of cables	10	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	96 mm	Clamping range	10 x 1 - 12.2 mm
Width	44 mm		

KEL-DP 16|11 A gy

Part No.	43461	Height	12 mm
EAN	4251269320767	Mounting height	5 mm
PU	10	Cut-out size	86 x 36 mm
For max. no. of cables	11	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	96 mm	Clamping range	3 x 1 - 10.5 mm
Width	44 mm		8 x 1 - 12.6 mm

KEL-DP 16|20 A gy

Part No.	43462	Height	12 mm
EAN	4251269320774	Mounting height	5 mm
PU	10	Cut-out size	86 x 36 mm
For max. no. of cables	20	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	96 mm	Clamping range	20 x 1 - 8.3 mm
Width	44 mm		

KEL-DP 16|22 A gy

Part No.	43463	Height	12 mm
EAN	4251269320781	Mounting height	5 mm
PU	10	Cut-out size	86 x 36 mm
For max. no. of cables	22	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	96 mm	Clamping range	5 x 1 - 12.1 mm
Width	44 mm		4 x 1 - 8.3 mm
			13 x 1 - 6.5 mm

KEL-DP 16|23 A gy

Part No.	43464	Height	12 mm
EAN	4251269320798	Mounting height	5 mm
PU	10	Cut-out size	86 x 36 mm
For max. no. of cables	23	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	96 mm	Clamping range	18 x 1 - 6.5 mm
Width	44 mm		5 x 1 - 12.1 mm

KEL-DP 16|26 A gy


Part No.	43465	Height	12 mm
EAN	4251269320804	Mounting height	5 mm
PU	10	Cut-out size	86 x 36 mm
For max. no. of cables	26	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	96 mm	Clamping range	19 x 1 - 6.5 mm
Width	44 mm		7 x 1 - 8.3 mm

KEL-DP 10|8 A gy

Part No.	43466	Height	12 mm
EAN	4251269324000	Mounting height	5 mm
PU	10	Cut-out size	65 x 36 mm
For max. no. of cables	8	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	75 mm	Clamping range	8 x 1 - 12.6 mm
Width	44 mm		

KEL-DP 10|12 A gy

Part No.	43467	Height	12 mm
EAN	4251269324017	Mounting height	5 mm
PU	10	Cut-out size	65 x 36 mm
For max. no. of cables	12	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	75 mm	Clamping range	4 x 1 - 6.5 mm
Width	44 mm		4 x 1 - 8.3 mm
			4 x 1 - 12.6 mm

KEL-DP 10|14 A gy


Part No. **43468**
 EAN **4251269324024**
 PU **10**
 For max. no. of cables **14**
 Color **grau (ähnlich RAL 7035)**
 Length **75 mm**
 Width **44 mm**

Height **12 mm**
 Mounting height **5 mm**
 Cut-out size **65 × 36 mm**
 For min. wall thickness **1,5 mm**
 For max. wall thickness **2,5 mm**
 Clamping range **14 x 1 - 8.3 mm**

KEL-DP 10|16 A gy


Part No. **43469**
 EAN **4251269324031**
 PU **10**
 For max. no. of cables **16**
 Color **grau (ähnlich RAL 7035)**
 Length **75 mm**
 Width **44 mm**

Height **12 mm**
 Mounting height **5 mm**
 Cut-out size **65 × 36 mm**
 For min. wall thickness **1,5 mm**
 For max. wall thickness **2,5 mm**
 Clamping range **4 x 1 - 6.5 mm**
12 x 1 - 12.6 mm

KEL-DP 10|26 A gy

Part No. **43470**
 EAN **4251269324048**
 PU **10**
 For max. no. of cables **26**
 Color **grau (ähnlich RAL 7035)**
 Length **75 mm**
 Width **44 mm**

Height **12 mm**
 Mounting height **5 mm**
 Cut-out size **65 × 36 mm**
 For min. wall thickness **1,5 mm**
 For max. wall thickness **2,5 mm**
 Clamping range **26 x 1 - 6.5 mm**

KEL-DP 6|6 A gy


Part No. **43450**
 EAN **4251269320712**
 PU **10**
 For max. no. of cables **6**
 Color **grau (ähnlich RAL 7035)**
 Length **62 mm**
 Width **44 mm**

Height **12 mm**
 Mounting height **5 mm**
 Cut-out size **52 × 36 mm**
 For min. wall thickness **1,5 mm**
 For max. wall thickness **2,5 mm**
 Clamping range **6 x 1 - 12.1 mm**

KEL-DP 6|12 A gy

Part No. **43451**
 EAN **4251269320729**
 PU **10**
 For max. no. of cables **12**
 Color **grau (ähnlich RAL 7035)**
 Length **62 mm**
 Width **44 mm**

Height **12 mm**
 Mounting height **5 mm**
 Cut-out size **52 × 36 mm**
 For min. wall thickness **1,5 mm**
 For max. wall thickness **2,5 mm**
 Clamping range **8 x 1 - 6.5 mm**
2 x 1 - 12.6 mm
2 x 1 - 16.1 mm

KEL-DP 6|14 A gy

Part No. **43452**
 EAN **4251269320736**
 PU **10**
 For max. no. of cables **14**
 Color **grau (ähnlich RAL 7035)**
 Length **62 mm**
 Width **44 mm**

Height **12 mm**
 Mounting height **5 mm**
 Cut-out size **52 × 36 mm**
 For min. wall thickness **1,5 mm**
 For max. wall thickness **2,5 mm**
 Clamping range **10 x 1 - 6.5 mm**
4 x 1 - 10.5 mm

KEL-DP 6|25 A gy

Part No.	43453	Height	12 mm
EAN	4251269320743	Mounting height	5 mm
PU	10	Cut-out size	52 x 36 mm
For max. no. of cables	25	For min. wall thickness	1,5 mm
Color	grau (ähnlich RAL 7035)	For max. wall thickness	2,5 mm
Length	62 mm	Clamping range	21 x 1 - 5 mm
Width	44 mm		4 x 1 - 8.3 mm

KEL-DP-E 46|7 gy

Part No.	43585	Height	12 mm
EAN	4251269310287	Mounting height	5 mm
PU	10	For min. wall thickness	1,5 mm
For max. no. of cables	7	For max. wall thickness	2,5 mm
Color	grau (ähnlich RAL 7035)	Clamping range	5 x 1 - 8.3 mm
Length	62 mm		2 x 1 - 6.5 mm
Width	25 mm		

KEL-DP-E 46|7 bk

Part No.	50585	Height	12 mm
EAN	4251269315008	Mounting height	5 mm
PU	10	For min. wall thickness	1,5 mm
For max. no. of cables	7	For max. wall thickness	2,5 mm
Color	schwarz	Clamping range	5 x 1 - 8.3 mm
Length	62 mm		2 x 1 - 6.5 mm
Width	25 mm		

KEL-DP-E 46|9 gy

Part No.	43587	Height	12 mm
EAN	4251269310294	Mounting height	5 mm
PU	10	For min. wall thickness	1,5 mm
For max. no. of cables	9	For max. wall thickness	2,5 mm
Color	grau (ähnlich RAL 7035)	Clamping range	8 x 1 - 6.5 mm
Length	62 mm		1 x 1 - 12.1 mm
Width	25 mm		

KEL-DP-E 46|9 bk

Part No.	50587	Height	12 mm
EAN	4251269315015	Mounting height	5 mm
PU	10	For min. wall thickness	1,5 mm
For max. no. of cables	9	For max. wall thickness	2,5 mm
Color	schwarz	Clamping range	8 x 1 - 6.5 mm
Length	62 mm		1 x 1 - 12.1 mm
Width	25 mm		

KEL-DP-E 86|13 gy

Part No.	43581	Height	12 mm
EAN	4251269310263	Mounting height	5 mm
PU	10	For min. wall thickness	1,5 mm
For max. no. of cables	13	For max. wall thickness	2,5 mm
Color	grau (ähnlich RAL 7035)	Clamping range	11 x 1 - 8.3 mm
Length	102 mm		2 x 1 - 6.5 mm
Width	25 mm		

KEL-DP-E 86|13 bk

Part No.	50581	Height	12 mm
EAN	4251269314988	External diameter	mm
PU	10	Mounting height	5 mm
For max. no. of cables	13	For min. wall thickness	1,5 mm
Color	schwarz	For max. wall thickness	2,5 mm
Length	102 mm	Clamping range	11 x 1 - 8.3 mm
Width	25 mm		2 x 1 - 6.5 mm

KEL-DP-E 86|17 gy

Part No.	43583	Height	12 mm
EAN	4251269310270	Mounting height	5 mm
PU	10	For min. wall thickness	1,5 mm
For max. no. of cables	17	For max. wall thickness	2,5 mm
Color	grau (ähnlich RAL 7035)	Clamping range	16 x 1 - 6.5 mm
Length	102 mm		1 x 1 - 12.1 mm
Width	25 mm		

KEL-DP-E 86|17 bk

Part No.	50583	Height	12 mm
EAN	4251269314995	Mounting height	5 mm
PU	10	For min. wall thickness	1,5 mm
For max. no. of cables	17	For max. wall thickness	2,5 mm
Color	schwarz	Clamping range	16 x 1 - 6.5 mm
Length	102 mm		1 x 1 - 12.1 mm
Width	25 mm		

KEL-DP-E 112|16 gy

Part No.	43576	Height	12 mm
EAN	4251269310249	Mounting height	5 mm
PU	10	For min. wall thickness	1,5 mm
For max. no. of cables	16	For max. wall thickness	2,5 mm
Color	grau (ähnlich RAL 7035)	Clamping range	4 x 1 - 6.5 mm
Length	128 mm		11 x 1 - 8.3 mm
Width	25 mm		1 x 1 - 12.1 mm

KEL-DP-E 112|16 bk

Part No.	50576	Height	12 mm
EAN	4251269314964	Mounting height	5 mm
PU	10	For min. wall thickness	1,5 mm
For max. no. of cables	16	For max. wall thickness	2,5 mm
Color	schwarz	Clamping range	4 x 1 - 6.5 mm
Length	128 mm		11 x 1 - 8.3 mm
Width	25 mm		1 x 1 - 12.1 mm

KEL-DP-E 112|21 gy

Part No.	43578	Height	12 mm
EAN	4251269310256	Mounting height	5 mm
PU	10	For min. wall thickness	1,5 mm
For max. no. of cables	21	For max. wall thickness	2,5 mm
Color	grau (ähnlich RAL 7035)	Clamping range	16 x 1 - 6.5 mm
Length	128 mm		4 x 1 - 8.3 mm
Width	25 mm		1 x 1 - 12.1 mm

KEL-DP-E 112|21 bk

Part No.	50578	Height	12 mm
EAN	4251269314971	Mounting height	5 mm
PU	10	For min. wall thickness	1,5 mm
For max. no. of cables	21	For max. wall thickness	2,5 mm
Color	schwarz	Clamping range	16 x 1 - 6.5 mm
Length	128 mm		4 x 1 - 8.3 mm
Width	25 mm		1 x 1 - 12.1 mm

KEL-DP-S 69|8 gy

Part No.	43591	Height	12 mm
EAN	4251269310300	Mounting height	5 mm
PU	10	For min. wall thickness	1,5 mm
For max. no. of cables	8	For max. wall thickness	2,5 mm
Color	grau (ähnlich RAL 7035)	Clamping range	8 x 1 - 7.5 mm
Length	78 mm		
Width	19,5 mm		

KEL-DP-S 69|8 bk

Part No.	50591	Height	12 mm
EAN	4251269315022	Mounting height	5 mm
PU	10	For min. wall thickness	1,5 mm
For max. no. of cables	8	For max. wall thickness	2,5 mm
Color	schwarz	Clamping range	8 x 1 - 7.5 mm
Length	78 mm		
Width	19,5 mm		