

KEL-SCDP

Cable Entry Plate



Product Description

With the KEL-SCDP cable entry grommet, single cables, hoses, and conduit can be routed and sealed at a rating of IP65. Its unique advantage is the large sealing range. The single circular membrane can be peeled away to accommodate the specific diameter of the cable or hose. No tooling is required to peel off the membrane. The peeled-off area is always round, ensuring a secure seal around cable/hose.

Another advantage is the high mounting flexibility. The KEL-SCDP can simply be plugged into cut-outs with wall thicknesses from 1.5 to 4.0 mm.

Advantages & Benefits

- Perfect edge protection and sealing
- Circular membranes can be peeled off easily
- Easy, tool-less assembly
- Protection class up to IP65

Specifications

Material	Elastomer
IP rating	IP65
Temperature	- 40°C to + 80°C (static)
Properties	Halogen-free, silicone-free

Type	Order No.	Number of cables	Clamping range mm / "	PU
KEL-SCDP 25	43480	1 max.	5 – 16 / 1.20 - 0.63"	10
KEL-SCDP 32	43481	1 max.	5 – 22 / 1.20 - 0.87"	10
KEL-SCDP 40	43482	1 max.	8 – 28 / 0.31 - 1.10"	10
KEL-SCDP 50	43483	1 max.	8 – 36 / 0.31 - 1.42"	10



The single membrane rings are peeled off according to the diameter of the routed cable/hose. For this purpose, only a small hole between the rings needs to be pierced. Then the corresponding ring can be removed.

2.2