

## TYPE TIES

### Features

- Quick & Easy
- Strong & Flexible
- Nylon 6/6

### Benefits

- Can accommodate .75" to 15" bundle diameter
- Tensile strengths from 18 lbs to 250 lbs
- Resists weather & chemicals



Standard Cable Ties

Catalog Number	Length	Width	Color	Tensile Strength	Bundle Diameter	Bag Qty
93110	4.0	0.10	NATURAL	18 LBS.	.75	100
93110M	4.0	0.10	NATURAL	18 LBS.	.75	1000
93210	4.0	0.10	UV BLACK	18 LBS.	.75	100
93210M	4.0	0.10	UV BLACK	18 LBS.	.75	1000
93120	5.7	0.14	NATURAL	40 LBS.	1.25	100
93120M	5.7	0.14	NATURAL	40 LBS.	1.25	1000
93220	5.7	0.14	UV BLACK	40 LBS.	1.25	100
93220M	5.7	0.14	UV BLACK	40 LBS.	1.25	1000
93130	8	0.19	NATURAL	50 LBS.	2.0	100
93130M	8	0.19	NATURAL	50 LBS.	2.0	1000
93230	8	0.19	UV BLACK	50 LBS.	2.0	100
93230M	8	0.19	UV BLACK	50 LBS.	2.0	1000
93150	11.8	0.19	NATURAL	50 LBS.	3.0	100
93150M	11.8	0.19	NATURAL	50 LBS.	3.0	1000
93250	11.8	0.19	UV BLACK	50 LBS.	3.0	100
93250M	11.8	0.19	UV BLACK	50 LBS.	3.0	1000
93160	14.6	0.19	NATURAL	50 LBS.	4.0	100
93160M	14.6	0.19	NATURAL	50 LBS.	4.0	1000
93260	14.6	0.19	UV BLACK	50 LBS.	4.0	100
93260M	14.6	0.19	UV BLACK	50 LBS.	4.0	1000
93170	14.5	0.30	NATURAL	120 LBS.	4.0	100
93170D	14.5	0.30	NATURAL	120 LBS.	4.0	500
93270	14.5	0.30	UV BLACK	120 LBS.	4.0	100
93270D	14.5	0.30	UV BLACK	120 LBS.	4.0	500
93185	28	0.30	NATURAL	120 LBS.	8.0	100
93185D	28	0.30	NATURAL	120 LBS.	8.0	500
93285	28	0.30	UV BLACK	120 LBS.	8.0	100
93285D	28	0.30	UV BLACK	120 LBS.	8.0	500