

### TYPE TIES

#### Features

- Quick & Easy
- Strong & Flexible
- Nylon 6/6

#### Benefits

- Can accommodate .75" to 15" bundle diameter
- Tensile strengths from 18 lbs to 250 lbs
- Resists weather & chemicals



Mounting Head Cable Ties

Catalog Number	Length	Width	Bolt Size	Color	Tensile Strength	Bundle Diameter	Bag Qty
93310	4.5	.10	#4	NATURAL	18 LBS.	.62	100
93410	4.5	.10	#4	UV BLACK	18 LBS.	.62	100
93320	5.9	.14	#8	NATURAL	40 LBS.	1.25	100
93420	5.9	.14	#10	UV BLACK	40 LBS.	1.25	100
93340	8	.19	#10	NATURAL	50 LBS.	2	100
93440	8	.19	#10	UV BLACK	50 LBS.	2	100
93350	12.6	.19	#10	NATURAL	50 LBS.	3	100
93450	12.6	.19	#10	UV BLACK	50 LBS.	3	100
93380	15	.19	#10	NATURAL	50 LBS.	4	100
93480	15	.19	#10	UV BLACK	50 LBS.	4	100
93390	15	.30	#10	NATURAL	120 LBS.	4	100
93490	15	.30	#10	UV BLACK	120 LBS.	4	100

#### Push Mount Cable Ties

Catalog Number	Length	Width	Color	Tensile Strength	Bundle Diameter	Bag Qty
93345	7.9	.19	NATURAL	50 LBS.	2	100
93445	7.9	.19	UV BLACK	50 LBS.	2	100

#### Releasable Cable Ties

Catalog Number	Length	Width	Color	Tensile Strength	Bundle Diameter	Bag Qty
93620	5.9	.30	NATURAL	50 LBS.	1.2	100
93720	5.9	.30	UV BLACK	50 LBS.	1.2	100
93640	7.8	.30	NATURAL	50 LBS.	2	100
93740	7.8	.30	UV BLACK	50 LBS.	2	100
93650	10.5	.30	NATURAL	50 LBS.	3	100
93750	10.5	.30	UV BLACK	50 LBS.	3	100