

ILSCO Copper Two Bolt Connectors

RoHS
Compliant



TYPE IKB


Features

- Manufactured from high strength copper alloy
- Two bolt design
- Longer peened bolt
- Suitable for use in circuits rated 35KV or less, proper high voltage spacing and insulation techniques must be used
- For copper conductor only
- Rated to 90° C

Benefits

- Allows maximum conductivity and high breakage resistance
- Allows maximum pressure to be applied directly to the conductor strands
- Permits a swivel action for easier installation
- Application versatility

B



Catalog Number	Copper Wire Range		Dimensions		
	Main	Tap	C	H	W
IKB-4/0 +	1/0-4/0	4/0-10	1.10	1.97	1.72
IKB-350 +	350kcmil-250kcmil	350kcmil-10	1.38	2.48	2.14
IKB-500	500kcmil-400kcmil	500kcmil-10	1.50	2.80	2.25
IKB-800	800kcmil-400kcmil	800kcmil-3/0	1.62	3.32	2.50
IKB-1000	1000kcmil-500kcmil	1000kcmil-3/0	2.00	3.78	3.03

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

+ RUS Listed

Tested to UL 486A/B, UL File E6207

