

TYPE SGB

Features

- Manufactured from high strength 6061-T6 aluminum alloy
- Electro-tin plated
- Lay-in feature
- Stainless steel hardware
- Serrations in conductor wire way
- Unique clamp design
- 1/4" max frame thickness
- Meets ASTM B117-09

Benefits

- Suitable for use with copper or aluminum conductors
- Provides low contact resistance
- Provides ease of installation
- For corrosion resistance, greater torque and ease of installation
- Cuts oxidation
- No mounting hardware required, reusable
- Mount to solar panel frames
- Resistance to outdoor salt spray




Fig. 1




Fig. 2

Catalog Number	Figure Number	Ground Wire Range	Dimensions		
			L	W	H
SGB-4	1	4-14	1.375	.500	.940
SGB-5	2	4-14	1.375	.500	1.440

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

UL 467 for grounding and bonding. UL File E34440

UL2703 Recognized E354420 Vol. 1

DE-OX® oxide inhibitor is recommended for all aluminum terminations

Patent pending