

TYPE
IDT-6H

Features

- Dieless operation
- Flip top head
- Lightweight - 6.2 lbs
- Equipped with 3/8" male screw coupler

Benefits

- No dies to lose or replace, one tool does it all
- Easy connector loading and unloading
- Easy to hold, less tiring for numerous crimps
- For use with standard industry hoses

Specifications

Force developed: 6.2 Tons
 Operating pressure: 10,000 PSI
 Overall Length: 10-1/2"
 Weight: 6.2 lbs.
 Conductor Range: 750kcmil-#6



For Use with

Aluminum Connectors	Copper Connectors
ACL, ACN Series thru 750kcmil	CLN4, CLN9, CLND, CSLT, CLWU
2ACL, 2ACN Series thru 750kcmil	CLNF, CLNN, CLNS,
AS Series thru 750kcmil	CLNU, CLW4, CLW9,
IACL Series thru 500kcmil	CLWD, CLWF, CLWN,
2IACL Series thru 500kcmil	CLWS, CSN4, CSN9,
	CSND, CSNF, CSNN,
	CSNS, CSW4, CSW9,
	CSWD, CSWF, CSWN,
	CSWS 750kcmil thru 6

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

Additional Requirements:

- Hose
- Pump

Includes:

Steel Carrying Case
 Instruction Manual