

TYPE  
**ILC-12H-N**

**Features**

- Head tested to 50,000 crimp cycles
- Accepts industry standard "U" dies
- Hot stick attachment point
- Light head - 9.7 lbs
- Equipped with 3/8" male screw coupler
- Ram automatically retracts when crimp cycle is complete

**Benefits**

- Durable and dependable
- Flexibility and economy
- Offers the option of performing line maintenance when properly protected
- Easy to hold, less tiring for numerous crimps
- For use with standard industry hoses
- Confirms crimp was completed

**Specifications**

Force developed: 12 Tons  
 Operating pressure: 10,000 PSI  
 Weight: 9.7 lbs.  
 Overall Length: 11-7/8"  
 Jaw Opening: 1.65"  
 Conductor Range: 1000kcmil-#8



**For Use with\***

| <b>Aluminum Connectors</b> | <b>Copper Connectors</b>     |
|----------------------------|------------------------------|
| CPM Series                 | CLN4, CLN9, CLND, CSLT, CLWU |
| ACM Series                 | CLNF, CLNN, CLNS,            |
| ACO Series                 | CLNU, CLW4, CLW9,            |
| ACO-90 Series              | CLWD, CLWF, CLWN,            |
| ACL 750kcmil-8             | CLWS, CSN4, CSN9,            |
| 2ACL 750kcmil-1/0          | CSND, CSNF, CSNN,            |
| AS 750kcmil-8              | CSNS, CSW4, CSW9,            |
| AH 1-7                     | CSWD, CSWF, CSWN,            |
| HT Series                  | CSWS 1000kcmil thru 8        |
| IACL Series                |                              |
| 2IACL Series               |                              |

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)  
 \*See page 367 for required compression dies

**Additional Requirements:**

- Hose
- Pump

**Includes:**

Steel Carrying Case  
 Instruction Manual