

# ILSCO Ground Clamp with Strap

RoHS  
Compliant



## TYPE BGCS

### Features

- UL Listed and CSA Certified
  - Conduit hub for 1/2" thru 1" rigid conduit
  - Zinc plated screws
  - ETP copper strap
- For copper conductor only

### Benefits

- Ensures reliability
- Range taking
- Corrosion resistance
- Protects conduit system from vibrations and provides maximum conductivity



Catalog Number	Figure Number	Water Pipe Range	Conduit Hub Size	Ground Wire Range
CH-1	1	-	1	3/0 AWG - 10sol
CH-34	1	-	3/4	2/0 AWG - 10sol
J2124	2	2-1/2-4	-	4str - 10sol
J6	2	4-1/2-6	-	4str - 10sol
BGC-1-50S	3	1/2-1	1/2	8sol - 4str
BGC-1-75S	3	1/2-1	3/4	8sol - 4str
BGC-1-10S	3	1/2-1	1	8sol - 4str
BGC-1-50SH	4	1/2-1	1/2	2/0 - 10
BGC-1-75SH	4	1/2-1	3/4	2/0 - 10
BGC-1-10SH	4	1/2-1	1	2/0 - 10

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)  
UL File E207816

G

