

TYPE ILST-22K

Features

- Kit includes case and (5) dies
- Full cycle ratchet
- Compound action
- Cushion grip handles
- Crimps non-insulated, insulated, and double insulated wire terminals
- Wire Range: 10-22 AWG ILSCON connectors

Benefits

- All-in-one, ease of use
- Assures proper crimp force every time
- Delivers maximum crimp force with minimum effort
- Provides user comfort
- Optimum versatility, crimps all ILSCON connectors
- Provides flexibility in use



		UL Listed for use with				
		A	B	C	D1322	FA
DIE INDEX	PRODUCT FAMILIES	NBFTD	NFBRD	NBFT	BFBR	NFLB
		NBMTD	NFBRF	NBMT	BRBR	
		NBSS	NPBRD	NDFT	BSBR	
		NDFTD	NPRBD	NDMT	BSFBR	
		NDMTD	NRBRD	NFIDT	BSLBR	
		NFLBD	NSBRD	NFIFT	NFBR	
		NPBR	NSFBRD	NFIMT	CSWS-10*	
		NRBR	NSLBRD	VBFT		
		NSBR		VBMT		
		NSFBR		VDFT		
		NSLBR		VDMT		
		VBSS		VFIBT		
		VBST		VFIDT		
		VFBR				
		VPBR				
		VRBR				
VSB						
VSFBR						
VSLBR						

* UL Listed and CSA Certified

TYPE ILST-MP

Features

- Heavy duty carbon steel construction
- Comfort grip handles
- Color coded crimp nest
- Crimp nest and indenter
- Wire cutter
- Machine screw cutters
- Wire stripper/wire gauge

Benefits

- Rugged, durable, reliable
- Provides user comfort
- For insulated terminals
- For uninsulated terminals
- Easily cuts solid and stranded wire
- Cuts and rethreads 4-40, 6-32, 8-32, 10-24, and 10-32 machine screws
- 8-26 AWG



All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)