






SCREW: NONE	MATERIAL: COPPER	REV: E	 <small>connections matter</small> 800-776-9775 www.ilSCO.com
CAT. NO.: SEE CHART	PLATING: EL-TIN	DRAWN BY: DW SCALE: NTS	
INFORMATION SHEET: FORM 157	MARKING: SEE CHART	DATE: 6/3/2008 SIZE: B	
			DWG NO: Y1003-D-4 SHEET: 1 OF 1



DETAIL C
INK MARK TOP & BOTTOM

CATALOG NUMBER	"A"	"C"	"D"	"E"	"F"	"G"	TANG MARKING
CLNB-4/0-14-12-4	2.789	0.219	0.281	0.999	1.998	0.180	
CLNB-4/0-14-58-4	2.976	0.344	0.281	0.999	1.998	0.180	
CLNB-4/0-14-34-4	2.976	0.469	0.281	0.999	1.998	0.180	
CLNB-4/0-14-1-4	3.226	0.719	0.281	0.999	1.998	0.180	
CLNB-4/0-516-58-4	2.976	0.282	0.343	0.999	1.998	0.180	
CLNB-4/0-516-34-4	3.226	0.407	0.343	0.999	1.998	0.180	
CLNB-4/0-516-78-4	3.226	0.532	0.343	0.999	1.998	0.180	
CLNB-4/0-516-1-4	3.476	0.657	0.343	0.999	1.998	0.180	
CLNB-4/0-516-134-4	4.039	1.407	0.343	0.999	1.998	0.180	
CLNB-4/0-38-34-4	3.226	0.344	0.406	0.999	1.998	0.211	
CLNB-4/0-38-78-4	3.476	0.469	0.406	0.999	1.998	0.211	
CLNB-4/0-38-1-4	3.476	0.594	0.406	0.999	1.998	0.211	ILSCO, CLNB-40-38-1-4, 3/8 X 1, 4/0 AWG, 3/0 FLEX, DIE 54, UL, CSA
CLNB-4/0-38-116-4	3.476	0.656	0.406	0.999	1.998	0.211	
CLNB-4/0-38-118-4	3.664	0.719	0.406	0.999	1.998	0.211	
CLNB-4/0-38-134-4	4.164	1.344	0.406	0.999	1.998	0.211	
CLNB-4/0-38-2-4	4.539	1.594	0.406	0.999	1.998	0.211	
CLNB-4/0-12-1-4	3.664	0.438	0.562	0.999	1.998	0.265	
CLNB-4/0-12-114-4	4.039	0.688	0.562	0.999	1.998	0.265	
CLNB-4/0-12-112-4	4.164	0.938	0.562	0.999	1.998	0.265	
CLNB-4/0-12-134-4	4.539	1.188	0.562	0.999	1.998	0.265	ILSCO, C-4/0-12-134-4, 1/2 X 1-3/4, 45°, 4/0 AWG, 3/0 FLEX, DIE 54, UL, CSA
CLNB-4/0-12-178-4	4.539	1.313	0.562	0.999	1.998	0.265	

THE INFORMATION CONTAINED WITHIN THIS DOCUMENT IS PROPRIETARY TO ILSCO AND MAY NOT BE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT