





SCREW: NONE	MATERIAL: COPPER	REV: C	 800-776-9775 www.ilSCO.com
CAT. NO.: SEE CHART	PLATING: EL-TIN	DRAWN BY: DW SCALE: NTS	
INFORMATION SHEET: FORM 157	MARKING: SEE CHART	DATE: 6/3/2008 SIZE: B	
			DWG NO: Y1003-D-9
			SHEET: 1 OF 1



DETAIL C
INK MARK TOP & BOTTOM



CATALOG NUMBER	"A"	"C"	"D"	"E"	"F"	"G"	TANG MARKING
CLNB-4/0-14-12-9	2.038	0.219	0.281	0.999	2.233	0.180	UL, ILSCO, CSA, CLNB-4/0-14-12-9, 1/4 x 1/2, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-14-58-9	2.225	0.344	0.281	0.999	2.233	0.180	UL, ILSCO, CSA, CLNB-4/0-14-58-9, 1/4 x 5/8, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-14-34-9	2.225	0.469	0.281	0.999	2.233	0.180	UL, ILSCO, CSA, CLNB-4/0-14-34-9, 1/4 x 3/4, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-14-1-9	2.475	0.719	0.281	0.999	2.233	0.180	UL, ILSCO, CSA, CLNB-4/0-14-1-9, 1/4 x 1, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-516-58-9	2.225	0.282	0.343	0.999	2.233	0.180	UL, ILSCO, CSA, CLNB-4/0-516-58-9, 5/16 x 5/8, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-516-34-9	2.475	0.407	0.343	0.999	2.233	0.180	UL, ILSCO, CSA, CLNB-4/0-516-34-9, 5/16 x 3/4, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-516-78-9	2.475	0.532	0.343	0.999	2.233	0.180	UL, ILSCO, CSA, CLNB-4/0-516-78-9, 5/16 x 7/8, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-516-1-9	2.725	0.657	0.343	0.999	2.233	0.180	UL, ILSCO, CSA, CLNB-4/0-516-1-9, 5/16 x 1, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-516-134-9	3.288	1.407	0.343	0.999	2.233	0.180	UL, ILSCO, CSA, CLNB-4/0-516-134-9, 5/16 x 1-3/4, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-38-34-9	2.475	0.344	0.406	0.999	2.233	0.211	UL, ILSCO, CSA, CLNB-4/0-38-34-9, 3/8 x 3/4, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-38-78-9	2.725	0.469	0.406	0.999	2.233	0.211	UL, ILSCO, CSA, CLNB-4/0-38-78-9, 3/8 x 7/8, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-38-1-9	2.725	0.594	0.406	0.999	2.233	0.211	UL, ILSCO, CSA, CLNB-4/0-38-1-9, 3/8 x 1, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-38-116-9	2.725	0.656	0.406	0.999	2.233	0.211	UL, ILSCO, CSA, CLNB-4/0-38-116-9, 3/8 x 1-1/6, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-38-118-9	2.913	0.719	0.406	0.999	2.233	0.211	UL, ILSCO, CSA, CLNB-4/0-38-118-9, 3/8 x 1-1/8, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-38-134-9	3.413	1.344	0.406	0.999	2.233	0.211	UL, ILSCO, CSA, CLNB-4/0-38-134-9, 3/8 x 1-3/4, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-38-2-9	3.788	1.594	0.406	0.999	2.233	0.211	UL, ILSCO, CSA, CLNB-4/0-38-2-9, 3/8 x 2, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-12-1-9	2.913	0.438	0.562	0.999	2.233	0.265	UL, ILSCO, CSA, CLNB-4/0-12-1-9, 1/2 x 1, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-12-114-9	3.288	0.688	0.562	0.999	2.233	0.265	UL, ILSCO, CSA, CLNB-4/0-12-114-9, 1/2 x 1-1/4, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-12-112-9	3.413	0.938	0.562	0.999	2.233	0.265	UL, ILSCO, CSA, CLNB-4/0-12-112-9, 1/2 x 1-1/2, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-12-134-9	3.788	1.188	0.562	0.999	2.233	0.265	UL, ILSCO, CSA, CLNB-4/0-12-134-9, 1/2 x 1-3/4, 4/0 AWG, 3/0 FLEX, DIE 54
CLNB-4/0-12-178-9	3.788	1.313	0.562	0.999	2.233	0.265	UL, ILSCO, CSA, CLNB-4/0-12-178-9, 1/2 x 1-7/8, 4/0 AWG, 3/0 FLEX, DIE 54