

## Surge Protection Device - Surge Protective Device, 6-Mode, 120/240 VAC 1Ph, Type 1 or Type 2, Indoor Metal, Connected Equipment Warranty 10yr

Item IG2240-IMSK



### PRODUCT DESCRIPTION

Intermatic's Smart Guard® Whole House Surge Protective Device provides coverage of your customer's big investment equipment, from appliances and computers, to HVAC equipment and TVs. This innovative SPD uses the IMODULE® with LED lights for quick and easy indication when protection has been compromised. A blue light indicates the SPD unit is ON and a green light indicates surge protection is active. Trusted, state-of-the-art TPMOV® (Thermally Protected Metal Oxide Varistor) surge protection technology eliminates the potentially hazardous failure modes that are commonly associated with standard MOV technology. Type 1 applications include outdoor installations before service entrances and utility meter cabinets. Type 2 applications include installations after service entrances. UL Listed to ANSI/UL 1449 3rd edition

### FEATURES

- ▶ Six Modes of protection
- ▶ TPMOV® surge protection technology
- ▶ Module Power Switch, included on IG2240-IMSK, enables convenient disconnection of power at the SPD when replacing IMODULES
- ▶ Includes three IMODULES with LED power and protection status lights
- ▶ IMODULES replace quickly and easily, eliminating the need to install a new SPD unit
- ▶ Tamper-proof IMODULE doors, will only open when IMODULE is being inserted
- ▶ Type 1 Enclosure for indoor applications in metal
- ▶ 10-year product warranty
- ▶ \$50,000 connected equipment warranty for 10 years on appliances and electronics
- ▶ UL certified to ANSI/UL 1449 4th edition

### APPLICATIONS

- ▶ Whole Home Protection

### TECHNICAL DATA

General	
Model Number	IG2240-IMSK
Description	Surge Protective Device, 6-Mode, 120/240 VAC 1Ph, Type 1 or Type 2, Indoor Metal, Connected Equipment Warranty 10yr
UPC Code	078275148697
Brand	Intermatic
Country of Origin (Intermatic)	MEXICO
Warranty Period	10-Year limited (Base) 3-Year limited (Modules)
Connected Equipment Warranty Period	10-Year limited
Connected Equipment Warranty Coverage (USD)	50000
Surge Protection Type	1; 2
Electrical Specifications	
Modes of Protection	6 (L1-N, L2-N, L1-G, L2-G, N-G, L1-L2)
Short Circuit Current Rating	10 kA
Nominal Discharge Current	10 kA
Maximum Surge Current Rating Per Phase	50 kA
Surge Protection Technology	TPMOV®
Maximum Continuous Operating Voltage (L-G)	300
Maximum Continuous Operating Voltage (L-L)	300
Maximum Continuous Operating Voltage (L-N)	150

Maximum Continuous Operating Voltage (N-G)	150
Voltage Protection Rating (L-G)	1500
Voltage Protection Rating (L-L)	1500
Voltage Protection Rating (L-N)	800
Voltage Protection Rating (N-G)	700
Phase	Single
Voltage	120/240 VAC Single-Phase

#### Control Specifications

Surge Protection LED Indicator	Blue; Green
--------------------------------	-------------

#### Mechanical Specifications

Number of Wire Leads	4
Enclosure Type	Indoor type 1 metal

#### Dimensions

Wire Lead Length (in)	32
Wire Size Max	#10 AWG, Tinned Copper

#### Benefits

Has Module Power Switch	Yes
-------------------------	-----

#### Packaging

Shipping Weight (lbs)	9.2
Unit Carton Dimensions (H x W x L) in	4.38 x 8.13 x 11.13 in


#### Environmental Specifications

Temperature (operation)	-31 °F to 185 °F / (-35 °C to 85 °C)
-------------------------	--------------------------------------

#### Standards and Certifications

UL Certification	cULus
UL Standard	Ansi/UL 1449 3rd Edition
California Proposition 65	DEHP

**DRAWINGS AND DIAGRAMS**



---

## ACCESSORIES



IG120RSM10K

IModule® Replacement Module for Smart Guard®