

## In-Wall Timer - 7-Day Standard Programmable Timer, 120 VAC, 12A, Light Almond

Item EJ600A



### PRODUCT DESCRIPTION

A 12 A rated timer that provides full 7-day programming capabilities with dusk-to-dawn functionality, ideal for use with medium to low power loads. \*NOTE: Not for use with sunlamps, saunas, or loads that could cause personal injury if timed incorrectly.

### FEATURES

- ▶ 7-day programmable schedules with 14 ON/OFF events
- ▶ Astronomic clock feature determines dawn and dusk times
- ▶ Automatic Daylight Saving Time (DST) adjustment
- ▶ Random mode varies ON/OFF schedule to provide a "lived-in" appearance
- ▶ Single or 3-way switch compatible installation
- ▶ Incandescent/fluorescent compatible
- ▶ Built-in rechargeable, non-serviceable battery backup
- ▶ Requires neutral connection
- ▶ Decorator switch plate not included

### APPLICATIONS

- ▶ Indoor Lighting Control
- ▶ Air Movement & Ventilation
- ▶ Outdoor Lighting Control

### TECHNICAL DATA

General	
Model Number	EJ600A
Description	7-Day Standard Programmable Timer, 120 VAC, 12A, Light Almond
UPC Code	078275127883
Brand	Intermatic
Country of Origin (Intermatic)	CHINA
Warranty Period	1-Year limited
Application Compatibilities	Incandescent; Fluorescent
Harmonized Code	9107.00.8000
Control Specifications	
Maximum ON/OFF Operations	14
Operation Mode	24 hour
Operation Features	Astronomic; Daylight Saving Time
Mechanism Type	Digital/Electrical
Backup Type	Battery
Backup Protection Time	100 Hours
Battery Type	Rechargeable
Battery Service Type	Non-Serviceable
Minimum ON/OFF Times	1 min
Mechanical Specifications	
Wall Plate Configurations	Single-Gang

### Dimensions

Product Dimensions (H x W x D) in	4.125 x 1.75 x 1.4375 in
-----------------------------------	--------------------------

### Material Specifications

Color	Light Almond
Includes Wall Plate	No

### Load Ratings

Resistive Heater	12 A, 1440 W
Tungsten (Incandescent) Range(s)	1800 W, single-gang; 1440 W, multi-gang
Ballast Fluorescent	4 A, 500 VA
Motor Load Ratings Ranges	1/2 HP
Incandescent Load Ratings (Single-Gang)	15 A, 120 VAC, 60 Hz
Incandescent Load Ratings (Multi-Gang)	12 A, 120 VAC, 60 Hz
Incandescent Single Gang Load Ratings Ranges	15 A, 120 VAC, 60 Hz
Incandescent Multi Gang Load Ratings Ranges	12 A, 120 VAC, 60 Hz
Inductive Load Ratings Ranges	500 VA, 120 VAC, 60 Hz

### Electrical Specifications

Input Voltage Range(s)	120 VAC, 60 Hz
Wiring Configurations	Single; 3-Way
Neutral Connection Required	Yes

### Environmental Specifications

Temperature (operation)	32 - 104 °F / 0 - 40 °C
-------------------------	-------------------------

### Packaging

Shipping Weight (lbs)	0.35
Unit Carton Dimensions (H x W x D) in	6.13 x 2.13 x 3 in

### Standards and Certifications

CSA Certification	cCSAus
California Proposition 65	DEHP